



JN204BG

### 250A 4 Way 125A Outgoers Glazed

#### Technical Features

##### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

##### Electric current

Rated current	250 A
---------------	-------

##### Equipment

With lock	No
Has neutral terminal block	Yes

##### Dimensions

Height	950 mm
Width	710 mm
Depth	178.40 mm

##### Cover, door

Number of cabinet doors	1
Door/cover is transparent	Yes

##### Materials

Material	Steel
RAL code	7035 9001
Colour	Light grey

##### Equipment

Has earthing terminal block	Yes
-----------------------------	-----

##### Safety

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Key lock Quarter turn lock

##### Sustainability

RoHS conform	Yes
--------------	-----