



41670002

Soc.out. earthing contact USA/CANADA NEMA 5-15 R, screw term., arsys, white gl.

Technical Features

Electric current

Rated current	15 A
---------------	------

Voltage

Rated voltage	125 V
Nominal voltage	125 - 125 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	White
RAL code	1013
Surface finish	Glossy
Material	Duroplastic
Treatment	Untreated

Dimensions

Height	71 mm
Width	71 mm
Built-in depth	19 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	NEMA
Rotated central insert	No
With hinged lid	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Cover, door

Type of lid	Without lid
-------------	-------------

Capacity

Number of modules	1
-------------------	---

Safety

Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	With imprint
Cover	Central cover plate
Protection	Without enhanced contact protection
Type of connection	With screw terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes