



947792501

SCHUKO sock. outl., enh. cont. prot., plug-in term, Int. mod. ins., brown matt

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 50 Hz

Materials

Colour Brown

RAL code 8017

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Dimensions

Height 55.50 mm

Width 55.50 mm

Number of units 1

Built-in depth flush-mounted boxes 32 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal

Mounting type Built in installation
Screw mounting

Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

Accessories

Has labelling field No

Capacity

Number of modules 1

Safety

With enhanced contact protection Yes

Impact resistance IK IK05

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

Cover Central cover plate

Protection Enhanced contact protection

Type of connection With plug-in terminals

Suitable for

integro

Sustainability

REACH-SVHC free

Yes

RoHS conform

Yes
