



EMN005

Multifunction stair case time lag switch

Technical Features

Frequency

Frequency 50 - 60 Hz

Electric current

Rated current 16 A

Capacity

Number of modules 1

Connectivity

Type of connection Screw terminal
Wire connection

Installation, mounting

Mounting on DIN rail

Lighting

Max. load fluorescent lamp parallel compensated 1000 VA

Max. load fluorescent lamp 3600 VA

Use conditions

Operating temperature -10 - 55 °C

Connection

Cross-section flexible conductor 1 - 6 mm²

Cross-section rigid conductor 1.5 - 10 mm²

Settings

Time delay 30 S - 10 Min

Dimensions

Width 17.50 mm

Depth 64 mm

Sustainability

REACH-SVHC free Yes