



ESL263S

**Humfree Contactor 63A, 2NO, 12V~ 50Hz & 12V DC**

**Technical Features**

**Connection**

Type of contacts	2NO
------------------	-----

**Electric current**

Rated current	63 A
---------------	------

**Capacity**

Number of modules	3
-------------------	---

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage Uimp	4000 V
Rated insulation voltage Ui	440 V
Rated operational voltage Ue	400 - 400 V
Command voltage AC	12 - 12 V
Command voltage DC	12 - 12 V

**Use conditions**

Operating temperature	-10 - 50 °C
-----------------------	-------------

**Use**

Category of use	AC-7a/AC-7b
-----------------	-------------

**Use conditions**

Storage/transport temperature	-40 - 80 °C
-------------------------------	-------------

**Endurance**

Number of mechanical operations	100000
---------------------------------	--------

**Texts**

Safety hint	Humfree contactors are not suitable for intensive use cases (powered 24/7) and in these cases industrial contactors must be used.
-------------	---

**Endurance**

Electric endurance in number of cycles	30000
--	-------

**Power**

Total power loss under IN	14.50 W
Inrush power absorbed	5.20 VA

**Dimensions**

Height	85 mm
Width	54 mm
Depth	60 mm

**Connection**

Number of contacts	2
--------------------	---

**Equipment**

Number of NO contacts	2
Number of NC contacts	0
With switch for manual switch	No

**Connection**

Cross-section flexible conductor	1.5 - 16 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 25 mm <sup>2</sup>

**Architecture**

Number of poles	2
-----------------	---

---

**Sustainability**

---

RoHS conform

Yes