



52303213

**On/off switch 2pole earthing contact, light control**

**Technical Features**

**Electric current**

Switching current	20 AX (200W LED (SBL))
-------------------	------------------------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Voltage**

Rated voltage	250 V
---------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Material	Metal Plastic
Treatment	Untreated

**Identification**

Assembly arrangement	Basic element
----------------------	---------------

**Connectivity**

Mounting type	Clamp mounting Screw connection
---------------	------------------------------------

**Controls and indicators**

Number of buttons	1
-------------------	---

**Dimensions**

Dimensions	71 x 71 mm
Built-in depth	31 mm
Built-in depth flush-mounted boxes	35 mm

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Architecture**

Control/operation element	Single rocker
---------------------------	---------------

**Electric current**

Rated current	20 A
---------------	------

**Texts**

Type of connection	With screw terminals
Lighting	With neon lamp unit For lighting and monitoring circuit
Switch mode	2-pole off

**Sustainability**

RoHS conform	Yes
--------------	-----