



JK20210BG

**250A 2+10 Way Hybrid TPN Board With Glazed Door**

**Technical Features**

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	250 A
---------------	-------

**Equipment**

With lock	Yes
Has neutral terminal block	Yes

**Capacity**

Number of modules	30
-------------------	----

**Dimensions**

Height	1250 mm
Width	465 mm
Depth	165.50 mm

**Cover, door**

Number of cabinet doors	1
Door/cover is transparent	Yes

**Materials**

Material	Steel
RAL code	7035
Colour	Light grey

**Equipment**

Has earthing terminal block	Yes
-----------------------------	-----

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Key lock Quarter turn lock

**Sustainability**

RoHS conform	Yes
--------------	-----