



GD10T

**Surface mounting enclosure**

**Technical Features**

**Voltage**

Nominal voltage	230 - 415 V
-----------------	-------------

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Equipment**

Number of rails	1
Number of rows	1
Has neutral terminal block	Yes

**Capacity**

Number of modules	10
-------------------	----

**Dimensions**

Height	140 mm
Width	250 mm
Depth	65 mm
Built-in depth	65 mm

**Cover, door**

Number of locks	0
-----------------	---

**Dimensions**

Number of width units	10
-----------------------	----

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Connection**

Number of conduit inlets	0
--------------------------	---

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Materials**

Material	Polystyrene (PS)
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	No
Has mounting plate	No

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK05

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes