




EV108



**Dimmer 1-10V, with display**

**Technical Features**

**Voltage**

Operating voltage 230 - 230 V

**Frequency**

Frequency 50 - 50 Hz

**Connectivity**

Dimming DALI No

**Power**

Power consumption during operation 3 VA

Power consumption standby 1 W

**Use conditions**

Operating temperature -10 - 45 °C

**Dimensions**

Height 85 mm

Width 71 mm

Depth 65 mm

**Connection**

Cross-section rigid conductor 1.5 - 10 mm<sup>2</sup>

Cross-section flexible conductor 1 - 16 mm<sup>2</sup>

**Capacity**

Number of modules 4

**Electric current**

Control current 1-10 V slave 50 mA

**Materials**

Colour Grey

**Texts**

Type of connection With screw terminals

Installation mode For mounting on DIN rail

Junction Connection for illuminated (max. 5 mA) or standard push-buttons