



387603

Rotary switch, change-over, Serie 1930/Glas/R.classic

Technical Features

| | |
|-------------------------|------------------------|
| Electric current | |
| Switching current | 10 AX (100W LED (SBL)) |

| | |
|-------------------------------|----------------|
| Installation, mounting | |
| Mounting on | Flush mounting |

| | |
|----------------|-------|
| Voltage | |
| Rated voltage | 250 V |

| | |
|------------------|------------------|
| Materials | |
| Material | Metal Plastic |

| | |
|-----------------------|---------------|
| Identification | |
| Assembly arrangement | Basic element |

| | |
|---------------------|---------------|
| Connectivity | |
| Mounting type | Claw mounting |

| | |
|--------------------------------|---|
| Controls and indicators | |
| Number of buttons | 0 |

| | |
|------------------------------------|------------|
| Dimensions | |
| Dimensions | 71 x 71 mm |
| Built-in depth | 32 mm |
| Built-in depth flush-mounted boxes | 35 mm |

| | |
|-------------------------------|------|
| Safety | |
| Ingress Protection (IP) class | IP20 |
| Impact resistance IK | IK05 |

| | |
|---------------------------|---------------------|
| Architecture | |
| Control/operation element | Short rotary handle |

| | |
|-------------------------|------|
| Electric current | |
| Rated current | 10 A |

| | |
|--------------------|----------------------|
| Texts | |
| Installation mode | With spreader claws |
| Type of connection | With screw terminals |
| Lighting | Without neon lamp |
| Switch mode | Off/change-over |

| | |
|-----------------------|-----|
| Sustainability | |
| RoHS conform | Yes |