



WNC160



IP55



**cubyko Socket Schuko screwless & childpro wall mounted grey IP55**

**Technical Features**

**Voltage**

Rated voltage	250 V
---------------	-------

**Electric current**

Rated current	16 A
---------------	------

**Use conditions**

Operating temperature	-15 - 30 °C
-----------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Polycarbonate (PC) Polypropylene (PP) Thermoplastic
Treatment	Untreated
Contains recycled material (% of total plastic weight)	24.1 %

**Dimensions**

Height	76 mm
Width	76 mm
Depth	63 mm
Number of units	2
Built-in depth flush-mounted boxes	0 mm
Built-in depth	65 mm
Height of P-touch band for labelling field	0 mm

**Connection**

Connector/plug type	Plug-in terminal
Conductor cross-section	1.0 - 2.5 mm <sup>2</sup>
Cross-section flexible conductor without wire end sleeve	1.0 - 2.5 mm <sup>2</sup>

**Installation, mounting**

Mounting on	Surface mounting
Mounting-/Connection Position	Horizontal

**Connectivity**

Type of connection	Plug-in connection
With claw mounting	No
Mounting type	Screw mounting

**Equipment**

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No
With lock	No

**Accessories**

Has labelling field	No
Pre-equipped with	Socket outlet

**Cover, door**

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

---

**Capacity**

Number of modules	1
-------------------	---

---

**Safety**

With enhanced contact protection	Yes
----------------------------------	-----

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP55
-------------------------------	------

Usable in higher IP class	IP55 with closed cover
---------------------------	------------------------

Locking type	Without lock
--------------	--------------

---

**Functions**

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

---

**Identification**

With imprint	No
--------------	----

---

**Texts**

Imprint	Without imprint
---------	-----------------

Cover	Complete housing
-------	------------------

Protection	Enhanced contact protection
------------	-----------------------------

Type of connection	With plug-in terminals
--------------------	------------------------

Labelling	Without labelling
-----------	-------------------

Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor
----------	--

---

**Suitable for**

cubyko
--------

---

**Sustainability**

Halogen free	Yes
--------------	-----

RoHS conform	Yes
--------------	-----