



75414003



Technical Features

Settings

Supported configuration mode

ETS

Voltage

Operating voltage over bus

21 - 32 V

Auxiliary tension

24 - 24 V

Materials

Colour

Light grey

Dimensions

Depth

70 mm

Dimensions

90 x 72 mm

Use conditions

Operating temperature

-5 - 45 °C

Texts

Installation mode

For installation in distribution box

Type of connection

With screw terminals

Sustainability

REACH-SVHC free

Yes

RoHS conform

Yes