



WXPPS12

IP66 10AX 1 Gang 2 Way Switch

Technical Features

Electric current	
Switching current	10 A

Installation, mounting	
Mounting on	Surface mounting

Voltage	
Rated voltage	250 V

Materials	
Colour	Light grey
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Untreated

Identification	
Assembly arrangement	Basic element with complete housing

Connectivity	
Mounting type	Screw mounting

Controls and indicators	
Number of buttons	1

Dimensions	
Dimensions	90 x 90 mm

Safety	
Ingress Protection (IP) class	IP66

Architecture	
Control/operation element	Single rocker

Electric current	
Rated current	10 A

Texts	
Installation mode	For flush-mounted and hollow wall mounting
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way

Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes