



KB190B

Insulated busbar 1P 100A prong 20mm² 57M

Technical Features

Electric current

Rated current 100 A

Architecture

Number of poles 1

Dimensions

Length 1000 mm

Voltage

Rated impulse withstand voltage Uimp 4000 V

Rated operational voltage Ue 415 - 415 V

Connection

Cross-section rigid conductor 20 mm²

Connector/plug type Phase busbar with pin

Capacity

Number of modules 57

Sustainability

RoHS conform Yes