



KB190C

**Insulated busbar 1P 100A prong 20mm<sup>2</sup> 24M**

**Technical Features**

**Electric current**

Rated current 100 A

**Architecture**

Number of poles 1

**Dimensions**

Length 420 mm

**Voltage**

Rated impulse withstand voltage Uimp 4000 V

Rated operational voltage Ue 415 - 415 V

**Connection**

Cross-section rigid conductor 20 mm<sup>2</sup>

Connector/plug type Phase busbar with pin

**Capacity**

Number of modules 24

**Sustainability**

RoHS conform Yes