



945702505

Power sock. outl. 12 V, impr. 20 A f. vehicle, Int. module inserts, anthr. matt

Technical Features

Voltage

Rated voltage	12 V
---------------	------

Electric current

Rated current	20 A
---------------	------

Materials

Colour	Anthracite
RAL code	7021
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	55.50 mm
Width	55.50 mm
Depth	60 mm

Connection

Connector/plug type	Ring lug
---------------------	----------

Connectivity

Mounting type	Built in installation Screw mounting
---------------	---

Equipment

Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	1
-------------------	---

Safety

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	Without imprint
Cover	Central cover plate
Protection	Without enhanced contact protection
Type of connection	With flat connection

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes