Product Datasheet
JG320U

JG220U

IP66 20A 3P UTILITY ISOLATOR

Technical Features

Architecture	
Number of poles	3
Type of pole	3P
Electric current	
Rated current	20 A
Acceptable current rating AC21	20 A
Acceptable current rating AC21 category A	20 A
Acceptable current rating AC22 category A	20 A
Voltage	
Rated operational voltage Ue	380 - 440 V
Rated insulation voltage Ui	440 V
Installation, mounting	
Nominal tightening torque	2 - 2 Nm
Dimensions	
Height	170 mm
Width	84 mm
Depth	87 mm
Safety	
Ingress Protection (IP) class	IP66
Use conditions	
Operating temperature	-5 - 40 °C
Connection	
Cross-section rigid conductor	2.5 - 4 mm^2
Frequency	
Frequency	50 - 60 Hz
Sustainability	
RoHS conform	Yes