



REA121X



**Indoor station AUDIO surface-mounted 2-wire polar white glossy touch**

**Technical Features**

**Materials**

Colour	Polar white
Material	Plastic Thermoplastic

**Dimensions**

Height	74.50 mm
Width	93 mm
Depth	16 mm
Dimensions	74.50 x 93 mm

**Use conditions**

Operating temperature	5 - 50 °C
Storage/transport temperature	5 - 50 °C

**Voltage**

Operating voltage over bus	24 - 24 V
----------------------------	-----------

**Electric current**

Current consumption during operation	180 mA
Current consumption (idle)	265 mA

**Screen**

With touch screen	No
-------------------	----

**Texts**

Installation mode	Screw fastening via supporting plate Flat surface-mounted installation or onto wall box For vertical mounting
Junction	For floor call push-button For optional additional power supply Connection terminal block with screw terminals

**Functions**

Door communication type	Audio
Volume control	Yes

**Connection**

Conductor cross-section	0 - 0 mm <sup>2</sup>
-------------------------	-----------------------

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Accessories**

Additional device connectable	No
-------------------------------	----