

2 Way Garage Consumer Unit 40A 30mA Type A RCCB IP55

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Architecture

Number of poles	2
-----------------	---

Functions

Has protection main switch	Yes
----------------------------	-----

Capacity

Number of modules	4
-------------------	---

Electric current

Rated current	40 A
---------------	------

Dimensions

Depth	82 mm
Height	110 mm
Width	180 mm

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

RAL code	7035
Colour	Light grey
Material	Steel

Connection

Number of accessible phases	2
-----------------------------	---

Scope of delivery

Number of earth leakage circuit breaker type A	1
Number of RCCB in enclosure	1

Safety

Impact resistance IK	IK08
Ingress Protection (IP) class	IP55

Sustainability

RoHS conform	Yes
--------------	-----