

**2 Way Garage Consumer Unit 40A 30mA Type A RCCB IP55**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Architecture**

Number of poles	2
-----------------	---

**Functions**

Has protection main switch	Yes
----------------------------	-----

**Capacity**

Number of modules	4
-------------------	---

**Electric current**

Rated current	40 A
---------------	------

**Dimensions**

Depth	82 mm
Height	110 mm
Width	180 mm

**Cover, door**

Interlockable	No
Door/cover is transparent	No

**Materials**

RAL code	7035
Colour	Light grey
Material	Steel

**Connection**

Number of accessible phases	2
-----------------------------	---

**Scope of delivery**

Number of earth leakage circuit breaker type A	1
Number of RCCB in enclosure	1

**Equipment**

With socket outlet	No
--------------------	----

**Safety**

Impact resistance IK	IK08
Ingress Protection (IP) class	IP55

**Sustainability**

RoHS conform	Yes
--------------	-----