



VD106PT

Sm.distr.,VD/IC<sup>2</sup>,surface,1row,6M,IP40,no terminals,AUS,white door

**Technical Features**

**Voltage**

Nominal voltage	400 - 400 V
-----------------	-------------

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	63 A
---------------	------

**Equipment**

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No

**Capacity**

Number of modules	6
-------------------	---

**Functions**

With conduit inlets	Yes
---------------------	-----

**Dimensions**

Height	170 mm
Width	134.50 mm
Depth	91 mm

**Cover, door**

Number of cabinet doors	1
Number of locks	0

**Dimensions**

Number of width units	6
-----------------------	---

**Cover, door**

Door/cover is transparent	No
Cabinet door type	Single door

**Materials**

Material	Plastic
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	No
Has mounting plate	No

**Materials**

Ultraviolet-resistant	No
-----------------------	----

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock Without lock
Glow wire test	650 °C
Protection class with door	IP40

---

**Sustainability**

---

Halogen free	Yes
RoHS conform	Yes

---