



WGXR121PAS

10A 2G press round switch;as

Technical Features

Electric current

Switching current 10 A

Voltage

Rated voltage 250 V

Architecture

Control/operation element Double push button

Materials

Colour Aurora silver

Surface finish Matt

Material Polycarbonate (PC)

Treatment Varnished

Transparent No

Dimensions

Height 86 mm

Width 86 mm

Depth 25 mm

Built-in depth flush-mounted boxes 35 mm

Controls and indicators

Number of buttons 2

Connectivity

Type of connection Screw terminal

Safety

Ingress Protection (IP) class IP20

Accessories

Has labelling field No

Texts

Switch mode 1-way

Suitable for

shark

Sustainability

RoHS conform Yes