



47431907

SCHUKO soc. out. "ZSV" imprint, S.1/B.3/B.7, orange matt

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Rated voltage	250 V
---------------	-------

Nominal voltage	250 - 250 V
-----------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Orange
--------	--------

RAL code	2003
----------	------

Surface finish	Matt
----------------	------

Material	Thermoplastic
----------	---------------

Treatment	Untreated
-----------	-----------

Dimensions

Height	71 mm
--------	-------

Width	71 mm
-------	-------

Number of units	1
-----------------	---

Built-in depth flush-mounted boxes	31 mm
------------------------------------	-------

Built-in depth	32 mm
----------------	-------

Connection

Connector/plug type	Plug-in terminal
---------------------	------------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Plug-in connection
--------------------	--------------------

Mounting type	Screw mounting Claw mounting
---------------	---------------------------------

Equipment

Connector/plug type socket outlet	SCHUKO
-----------------------------------	--------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

With round protective earth pin	No
---------------------------------	----

With signal lamp	No
------------------	----

With lock	No
-----------	----

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	1
-------------------	---

Safety

With enhanced contact protection	No
----------------------------------	----

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP20
-------------------------------	------

Functions

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

Texts

Imprint	With imprint "ZSV"
Cover	Central cover plate
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

Suitable for

S.x/B.x