



ATA123008014

**Trunking 12x30,L=2,1m,brown**

**Technical Features**

**Dimensions**

Height	13 mm
Width	32 mm
Length	2100 mm
Inner cross-section	330 - 330 mm <sup>2</sup>

**Capacity**

Max. number of cables (Ø11mm, 50% filled, without devices)	2
--	---

**Materials**

Material	Polyvinylchloride (PVC)
Treatment	Untreated
RAL code	8014
Colour	Brown

**Safety**

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

**Standards**

Suitable for functional integrity according to DIN4102-12	No
---	----

**Use conditions**

Operating temperature	-5 - 65 °C
-----------------------	------------

**Connectivity**

Trunking coupling	Without coupling
-------------------	------------------

**Equipment**

Number of partitions	0
Number of pluggable partitions	0
Cable retaining clip included	Yes
With protective film	No

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes