

**Switch X160 3P 160A**

**Technical Features**

**Electric current**

Rated current	160 A
Rated short-time withstand current I <sub>cn</sub> IEC 60947	2 kA

**Architecture**

Number of poles	3
Control/operation element	Toggle

**Connection**

Cross-section rigid conductor	4 - 95 mm <sup>2</sup>
Cross-section flexible conductor	4 - 70 mm <sup>2</sup>

**Voltage**

Rated insulation voltage U <sub>i</sub>	690 V
Rated impulse withstand voltage U <sub>imp</sub>	8000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Functions**

Trip unit	Switch
-----------	--------