



WGDL111BEG

### 10A 1G bell switch mark bell symbol;eg

#### Technical Features

##### Electric current

|                   |      |
|-------------------|------|
| Switching current | 10 A |
|-------------------|------|

##### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

##### Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

##### Materials

|                |                    |
|----------------|--------------------|
| Colour         | Gold               |
| Surface finish | Matt               |
| Material       | Polycarbonate (PC) |
| Treatment      | Varnished          |
| Transparent    | No                 |

##### Dimensions

|                                    |       |
|------------------------------------|-------|
| Height                             | 86 mm |
| Width                              | 86 mm |
| Depth                              | 25 mm |
| Built-in depth flush-mounted boxes | 35 mm |

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Controls and indicators

|                              |    |
|------------------------------|----|
| Number of buttons            | 1  |
| With feedback signal contact | No |

##### Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

##### Texts

|             |                            |
|-------------|----------------------------|
| Imprint     | With imprinted symbol bell |
| Switch mode | 1-way                      |

##### Suitable for

|       |  |
|-------|--|
| shark |  |
|-------|--|

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |