



EC700

Pulses concentrator

Technical Features

Electric current

Number of entry circuits 7

Dimensions

Height 90 mm

Width 67 mm

Depth 50 mm

Safety

Ingress Protection (IP) class IP20

Installation, mounting

Mounting on DIN rail

Use conditions

Operating temperature -10 - 55 °C

Sustainability

REACH-SVHC free Yes

RoHS conform Yes