



UDBSQ06

### British Standard screed floor Box

#### Technical Features

##### Architecture

With carpet protection frame	Yes
With opening carpeting	Yes

##### Dimensions

Built-in depth	61 mm
Built-in width	273 mm
Built-in length	273 mm
Length	289 mm
Width	289 mm
Thickness of carpet recess	8 mm

##### Configuration

Installation size (underfloor installations)	Q06
--	-----

##### Installation, mounting

Suitable for recessed floor mounting	No
Suitable for concrete installation	Yes
Suitable for outdoor usage	No
Suitable for raised floor installation	Yes
Suitable for wet cleaning	No

##### Materials

Material	Metal Plastic
----------	------------------

##### Cover, door

Material cover	Polyamide (PA)
----------------	----------------

##### Use conditions

Vertical load applied across large surface area (heavy load)	5 kN
Vertical load applied across small surface area	3 kN

##### Functions

Suitable for sub-floor duct	Yes
-----------------------------	-----

##### Texts

Cable outlet	Without cable outlet in cover
--------------	-------------------------------

##### Materials

Colour	Light grey
RAL code	7035

##### Connection

Number of conduit inlets	8
--------------------------	---

##### Equipment

Number of outlet boxes	3
------------------------	---

##### Safety

Ingress Protection (IP) class	IP20
Protection class in unused condition	IP30

##### Sustainability

REACH-SVHC free	Yes
-----------------	-----