



UDBSQ06

British Standard screed floor Box

Technical Features

Architecture

With carpet protection frame	Yes
With opening carpeting	Yes

Dimensions

Built-in depth	61 mm
Built-in width	273 mm
Built-in length	273 mm
Length	289 mm
Width	289 mm
Thickness of carpet recess	8 mm

Configuration

Installation size (underfloor installations)	Q06
--	-----

Installation, mounting

Suitable for recessed floor mounting	No
Suitable for concrete installation	Yes
Suitable for outdoor usage	No
Suitable for raised floor installation	Yes
Suitable for wet cleaning	No

Materials

Material	Metal Plastic
----------	------------------

Cover, door

Material cover	Polyamide (PA)
----------------	----------------

Use conditions

Vertical load applied across large surface area (heavy load)	5 kN
Vertical load applied across small surface area	3 kN

Functions

Suitable for sub-floor duct	Yes
-----------------------------	-----

Texts

Cable outlet	Without cable outlet in cover
--------------	-------------------------------

Materials

Colour	Light grey
RAL code	7035

Connection

Number of conduit inlets	8
--------------------------	---

Equipment

Number of device casings	3
Number of outlet boxes	3

Safety

Ingress Protection (IP) class	IP20
Protection class in unused condition	IP30

Sustainability

REACH-SVHC free	Yes
-----------------	-----