



47661909

3gang SCHUKO soc. out. cover plate, S.1, p. white, matt, plastic

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white

RAL code 9010

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Dimensions

Height 80.50 mm

Width 151.50 mm

Number of units 3

Connection

Connector/plug type Plug-in terminal

Conductor cross-section 1.0 - 2.5 mm²

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Plug-in connection

Mounting type Screw mounting

Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

Accessories

Has labelling field No

Capacity

Number of modules 3

Safety

With enhanced contact protection No

Impact resistance IK IK05

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

Cover Full cover plate

Texts

Wiring	Through-wiring possible
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes