



WGDT2RJRJ6

RJ11 + RJ45 cat6 outlet

Technical Features

Frequency	
Transmission bandwidth	0-250 MHz
Equipment	
With transparent label holder	No
Number of outputs	2
Use conditions	
Operating temperature	-20-45 °C
Equipment	
With hinged lid	No
Materials	
Colour	White
Connection	
Connector/plug type	RJ45
Materials	
Material	Polycarbonate (PC)
Safety	
Ingress Protection (IP) class	IP20
Voltage	
Rated voltage	0 V
Electric current	
Rated current	0 A
Dimensions	
Built-in depth	27 mm
Texts	
Outlet	With straight outlet
Protection	With dust protection sliders
Supporting plate/supporting ring	With supporting plate
Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes