



47661939

3gang SCHUKO soc. out. cover plate, S.1, al., matt, lacq.

#### Technical Features

##### Voltage

Rated voltage	250 V
---------------	-------

##### Electric current

Rated current	16 A
---------------	------

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Materials

Colour	Aluminium
RAL code	9006
Surface finish	Matt
Material	Thermoplastic
Treatment	Varnished

##### Dimensions

Height	80.50 mm
Width	151.50 mm
Depth	41.60 mm

##### Connection

Conductor cross-section	1.0 - 2.5 mm <sup>2</sup>
-------------------------	---------------------------

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting

##### Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	3
-------------------	---

##### Safety

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

##### Functions

With orientation lighting	No
With function lighting	No

##### Identification

With imprint	No
--------------	----

##### Texts

Cover	Full cover plate
Wiring	Through-wiring possible

---

**Texts**

Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

---

**Suitable for**

S.x/B.x

---