



47661939

3gang SCHUKO soc. out. cover plate, S.1, al., matt, lacq.

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	Aluminium
RAL code	9006
Surface finish	Matt
Material	Thermoplastic
Treatment	Varnished

Dimensions

Height	80.50 mm
Width	151.50 mm
Depth	41.60 mm

Connection

Conductor cross-section	1.0 - 2.5 mm ²
-------------------------	---------------------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting

Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	3
-------------------	---

Safety

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	Without imprint
Cover	Full cover plate
Wiring	Through-wiring possible

Texts

Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

Suitable for

S.x/B.x
