




EE820



Motion detector Infrared 140°, IP55, wall mounted, white

Technical Features

Detection

Detection angle	140 -140 °
Type of sensor	Movement detector

Settings

Time delay	5 S - 15 Min
------------	--------------

Lighting

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Recommended installation height	2.50 - 2.50 m
---------------------------------	---------------

Use conditions

Operating temperature	-20 - 55 °C
-----------------------	-------------

Materials

Colour	White
Material	Plastic

Safety

Ingress Protection (IP) class	IP55
-------------------------------	------

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	Yes

Texts

Function	Can only be used as individual unit
Installation mode	For wall and ceiling mounting, corner installation with adapter
Type of connection	With plug-in terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes