




Motion detector Infrared 140°, IP55, wall mounted, white

EE820



**Technical Features**

**Detection**

Detection angle	140 -140 °
Type of sensor	Movement detector

**Settings**

Time delay	5 S - 15 Min
------------	--------------

**Lighting**

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Dimensions**

Recommended installation height	2.50 - 2.50 m
---------------------------------	---------------

**Use conditions**

Operating temperature	-20 - 55 °C
-----------------------	-------------

**Materials**

Colour	White
Material	Plastic

**Safety**

Ingress Protection (IP) class	IP55
-------------------------------	------

**Installation, mounting**

Mounting on	Surface mounting
Suitable for outdoor usage	Yes

**Texts**

Function	Can only be used as individual unit
Installation mode	For wall and ceiling mounting, corner installation with adapter
Type of connection	With plug-in terminals

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes