



ATA207529016

Trunking 20x75,L=2,0m,traffic white

Technical Features

Dimensions

Height	20 mm
Width	74 mm
Length	2000 mm
Inner cross-section	1296 - 1296 mm ²

Capacity

Max. number of cables (Ø11mm, 50% filled, without devices)	7
--	---

Materials

Material	Polyvinylchloride (PVC)
Treatment	Untreated
RAL code	9016
Colour	Traffic white

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

Standards

Suitable for functional integrity according to DIN4102-12	No
---	----

Use conditions

Operating temperature	-5 - 65 °C
-----------------------	------------

Connectivity

Trunking coupling	Without coupling
-------------------	------------------

Equipment

Number of partitions	2
Number of compartments	3 - 3
Number of pluggable partitions	0
Cable retaining clip included	Yes
With protective film	No

Installation, mounting

Base perforation	No
------------------	----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

