Product Datasheet
HIC425G

HIC425G

Automatic transfer switch 4x 250A

Technical Features

Voltage

Rated operational voltage Ue	380 - 415 V

Electric current

Rated current	250 A
Rated conditional short-circuit current Icc with gI-gG fuses	50 kA

Power

Rated operational power under 400 V AC AC1	164000 W

Architecture

Number of poles	4
Device construction type	Fixed built-in

Compatibility

Suitable for DIN Rail	No
Suitable for distribution board	Yes

Installation, mounting

Mounting on	Mounting plate

Sustainability

REACh-SVHC free	Yes