



WGCXL131FNB

**16AX 3G 1W switch w/fluorescence;nb**

**Technical Features**

**Electric current**

|                   |      |
|-------------------|------|
| Switching current | 16 A |
|-------------------|------|

**Voltage**

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

**Materials**

|        |        |
|--------|--------|
| Colour | Bronze |
|--------|--------|

|                |      |
|----------------|------|
| Surface finish | Matt |
|----------------|------|

|          |                    |
|----------|--------------------|
| Material | Polycarbonate (PC) |
|----------|--------------------|

|           |           |
|-----------|-----------|
| Treatment | Varnished |
|-----------|-----------|

**Controls and indicators**

|                   |   |
|-------------------|---|
| Number of buttons | 3 |
|-------------------|---|

**Dimensions**

|            |            |
|------------|------------|
| Dimensions | 86 x 86 mm |
|------------|------------|

|                                    |       |
|------------------------------------|-------|
| Built-in depth flush-mounted boxes | 35 mm |
|------------------------------------|-------|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Architecture**

|                           |               |
|---------------------------|---------------|
| Control/operation element | Triple rocker |
|---------------------------|---------------|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

**Texts**

|             |       |
|-------------|-------|
| Switch mode | 1-way |
|-------------|-------|

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|