



85346126



**KNX radio motion det. comf 2.2 m quicklink, Q.x, ant. velvety, lacq.**

**Technical Features**

**Dimensions**

|                                 |               |
|---------------------------------|---------------|
| Installation height             | 2.20 - 2.20 m |
| Recommended installation height | 2.20 - 2.20 m |

**Settings**

|                              |           |
|------------------------------|-----------|
| Supported configuration mode | quicklink |
| Minimal duty cycle           | 1 s       |

**Functions**

|                    |         |
|--------------------|---------|
| Maximal duty cycle | 180 min |
|--------------------|---------|

**Connectivity**

|                           |     |
|---------------------------|-----|
| With bus system KNX radio | Yes |
|---------------------------|-----|

**Scope of delivery**

|                         |     |
|-------------------------|-----|
| Bus connection included | Yes |
|-------------------------|-----|

**Lighting**

|                                |             |
|--------------------------------|-------------|
| Response brightness adjustable | 5 - 1000 lx |
|--------------------------------|-------------|

**Detection**

|                            |           |
|----------------------------|-----------|
| Detection angle adjustable | 45 - 90 ° |
| Detection angle horizontal | 90 - 180  |

**Use conditions**

|                       |            |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

**Materials**

|          |               |
|----------|---------------|
| Material | Thermoplastic |
|----------|---------------|

**Texts**

|          |   |
|----------|---|
| Function | Switch-off pre-warning on dimmer inserts<br>With memory function for presence simulation<br>Teach function for response brightness via button<br>With keylock<br>Party function for switching on for 2 hours<br>Reset function (to factory setting) |
|----------|---|

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|