



85346126



KNX radio motion det. comf 2.2 m quicklink, Q.x, ant. velvety, lacq.

Technical Features

Dimensions

Installation height	2.20 - 2.20 m
Recommended installation height	2.20 - 2.20 m

Settings

Supported configuration mode	quicklink
Minimal duty cycle	1 s

Functions

Maximal duty cycle	180 min
--------------------	---------

Connectivity

With bus system KNX radio	Yes
---------------------------	-----

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Lighting

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

Detection

Detection angle adjustable	45 - 90 °
Detection angle horizontal	90 - 180

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Materials

Material	Thermoplastic
----------	---------------

Texts

Function	Switch-off pre-warning on dimmer inserts With memory function for presence simulation Teach function for response brightness via button With keylock Party function for switching on for 2 hours Reset function (to factory setting)
----------	---

Sustainability

RoHS conform	Yes
--------------	-----