



WGDL111B

**10A 1G bell switch mark bell symbol**

**Technical Features**

**Electric current**

Switching current 10 A

**Voltage**

Rated voltage 250 V

**Architecture**

Control/operation element Single rocker

**Materials**

Colour White

Surface finish Glossy

Material Polycarbonate (PC)

Treatment Untreated

Transparent No

**Dimensions**

Height 86 mm

Width 86 mm

Depth 25 mm

Built-in depth flush-mounted boxes 35 mm

**Installation, mounting**

Mounting on Flush mounting

**Controls and indicators**

Number of buttons 1

With feedback signal contact No

**Connectivity**

Type of connection Screw terminal

**Safety**

Ingress Protection (IP) class IP20

**Accessories**

Has labelling field No

**Texts**

Imprint With imprinted symbol bell

Switch mode 1-way

**Suitable for**

shark

**Sustainability**

RoHS conform Yes