



WGDL111B

10A 1G bell switch mark bell symbol

Technical Features

Electric current

Switching current 10 A

Voltage

Rated voltage 250 V

Architecture

Control/operation element Single rocker

Materials

Colour White

Surface finish Glossy

Material Polycarbonate (PC)

Treatment Untreated

Transparent No

Dimensions

Height 86 mm

Width 86 mm

Depth 25 mm

Built-in depth flush-mounted boxes 35 mm

Installation, mounting

Mounting on Flush mounting

Controls and indicators

Number of buttons 1

With feedback signal contact No

Connectivity

Type of connection Screw terminal

Safety

Ingress Protection (IP) class IP20

Accessories

Has labelling field No

Texts

Imprint With imprinted symbol bell

Switch mode 1-way

Suitable for

shark

Sustainability

RoHS conform Yes