



WGDL111E

10A 1G press switch mark "exit"

Technical Features

Electric current		
Switching current		10 A
Voltage		
Rated voltage		250 V
Architecture		
Control/operation element		Single rocker
Materials		
Colour		White
Surface finish		Glossy
Material		Polycarbonate (PC)
Treatment		Untreated
Transparent		No
Dimensions		
Height		86 mm
Width		86 mm
Depth		25 mm
Built-in depth flush-mounted boxes		35 mm
Installation, mounting		
Mounting on		Flush mounting
Controls and indicators		
Number of buttons		1
With feedback signal contact		No
Connectivity		
Type of connection		Screw terminal
Safety		
Ingress Protection (IP) class		IP20
Accessories		
Has labelling field		No
Texts		
Imprint	With imprint " "	" and symbol key
Switch mode		1-way
Suitable for		
shark		
Sustainability		
RoHS conform		Yes