



16612049

**Rocker f.accessible const., guide f.mouth-held rod,clearlens,R.1/R.3,p.white gl.**

**Technical Features**

**Architecture**

Control/operation element Rocker with mouth rod guiding

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

**Dimensions**

Height	57.80 mm
Width	57.80 mm
Depth	9.55 mm

**Connectivity**

Mounting type Clamp mounting

**Equipment**

Monitoring window/light outlet Yes

**Accessories**

Has labelling field No

**Safety**

Ingress Protection (IP) class	IP44
Impact resistance IK	IK05

**Texts**

Imprint	Without imprint
Installation mode	Clamp fastening
Lighting	For lighting and monitoring circuit
Push button	Also for KNX applications: push-button, 1-gang, and group push-button, 1-gang
Rocker switch/rocker push-button	For rocker push-buttons For change-over/intermediate switch

**Suitable for**

R.x

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes