



16612049

Rocker f.accessible const., guide f.mouth-held rod,clearlens,R.1/R.3,p.white gl.

Technical Features

Architecture

Control/operation element	Rocker with mouth rod guiding
---------------------------	-------------------------------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	57.80 mm
Width	57.80 mm
Depth	9.55 mm

Connectivity

Mounting type	Clamp mounting
---------------	----------------

Equipment

Monitoring window/light outlet	Yes
--------------------------------	-----

Accessories

Has labelling field	No
---------------------	----

Safety

Ingress Protection (IP) class	IP44
Impact resistance IK	IK05

Texts

Imprint	Without imprint
Installation mode	Clamp fastening
Lighting	For lighting and monitoring circuit
Push button	Also for KNX applications: push-button, 1-gang, and group push-button, 1-gang
Rocker switch/rocker push-button	For rocker push-buttons For change-over/intermediate switch

Suitable for

Berker R.x	
------------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes