



16612049

Rocker f.accessible const., guide f.mouth-held rod,clearlens,R.1/R.3,p.white gl.

Technical Features

Architecture

Control/operation element Rocker with mouth rod guiding

Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	57.80 mm
Width	57.80 mm
Depth	9.55 mm

Connectivity

Mounting type Clamp mounting

Equipment

Monitoring window/light outlet Yes

Accessories

Has labelling field No

Safety

Ingress Protection (IP) class	IP44
Impact resistance IK	IK05

Texts

Imprint	Without imprint
Installation mode	Clamp fastening
Lighting	For lighting and monitoring circuit
Push button	Also for KNX applications: push-button, 1-gang, and group push-button, 1-gang
Rocker switch/rocker push-button	For rocker push-buttons For change-over/intermediate switch

Suitable for

R.x

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes