



FP75TN2

enclosure, univers, IP54, CL 1, 1100 x 1300 x 205 mm, exp., empty

Technical Features

Dimensions

Height	1100 mm
Width	1300 mm
Depth	205 mm
Thickness of sidewall	1 mm

Safety

Ingress Protection (IP) class	IP54
Protection class	Isolation class I
Locking type	Bar lock Without lock
Impact resistance IK	IK09

Equipment

Number of section in width	5
Number of flange plate openings	10

Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	No

Materials

Colour	Pure white
RAL code	9010
Treatment	Powder coated
Material	Steel

Equipment

Number of rows	7
----------------	---

Materials

Surface finish	Matt
----------------	------

Cover, door

Number of cabinet doors	2
Number of locks	1
Door/cover is transparent	No
Cabinet door type	Double door, asymmetric

Electric current

Rated current	250 A
---------------	-------

Sustainability

RoHS conform	Yes
--------------	-----