



WMQX



Quadplexer TV, FM/DAB, Satellite 1 & Satellite 2 Outlet

Technical Features

Connectivity

Mounting type	Screw mounting
---------------	----------------

Attenuation

Tap loss at 2150 MHz	1.50 dB
Tap loss at 860 MHz	2.50 dB

Frequency

Frequency bandwidth	5 - 2400 MHz
---------------------	--------------

Equipment

Number of outputs	4
-------------------	---

Materials

Material	Urea formaldehyde
Colour	White

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes