



WMQX



Quadplexer TV, FM/DAB, Satellite 1 & Satellite 2 Outlet

Technical Features

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Attenuation

| | |
|----------------------|---------|
| Tap loss at 2150 MHz | 1.50 dB |
| Tap loss at 860 MHz | 2.50 dB |

Frequency

| | |
|---------------------|--------------|
| Frequency bandwidth | 5 - 2400 MHz |
|---------------------|--------------|

Equipment

| | |
|-------------------|---|
| Number of outputs | 4 |
|-------------------|---|

Materials

| | |
|----------|-------------------|
| Material | Urea formaldehyde |
| Colour | White |

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Identification

| | |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |