



WMGS22RBSW

### 20A 2 Way Retractive Switch Brushed Steel White Insert

#### Technical Features

##### Electric current

|                   |      |
|-------------------|------|
| Switching current | 20 A |
|-------------------|------|

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

##### Materials

|                |                 |
|----------------|-----------------|
| Colour         | Stainless steel |
| Surface finish | Matt            |
| Material       | Stainless steel |
| Treatment      | Brushed         |

##### Identification

|                      |  |
|----------------------|--|
| Assembly arrangement | Basic element with central cover plate |
|----------------------|--|

##### Connectivity

|               |                  |
|---------------|------------------|
| Mounting type | Snap-on mounting |
|---------------|------------------|

##### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

##### Dimensions

|                |            |
|----------------|------------|
| Dimensions     | 59 x 25 mm |
| Built-in depth | 13.10 mm   |

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

##### Electric current

|               |      |
|---------------|------|
| Rated current | 20 A |
|---------------|------|

##### Texts

|             |  |
|-------------|--|
| Lighting    | Without lighting (cannot be illuminated) |
| Switch mode | 2-pole                                   |

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |